

Rev. 1910

LDP-V 03-100 V4.0

Driver Module for pulsed Lasers






Figure: Current monitor output, scale: -0.4 A/Div

Product Description

The LDP-V 03-100 is a small and inexpensive source for nanosecond pulses. The device is optimized for pulse repetition from single shot up to MHz repetition with duty cycles up to 100% **. Its typical application is driving pulsed laser diodes. Those can be mounted directly onto the LDP-V, eliminating the need for strip lines. The diode must be electrically isolated from earth (chassis) ground. Compatible packages: TO-18, TO-5, TO-52, 5.6 mm, 9 mm and similar. Despite its small size, the LDP-V is designed for ease of use. It eliminates the need for multiple peripheral supply units. A single 15.. 24 V DC supply and a triggering signal are all what is required for operation.

Additionally, the LDP-V can be extended with the PLCS-21 controller to enable USB 2.0 communication with a PC or the operating unit PLB-21.

Do not use PLCS-21 with higher supply voltage than 15 V. If you use the PLCS-21 with higher voltage than 15 V, the device will be damaged.

- Compact OEM module
- 0.3 to 3 A diode current
- < 1.2 ns rise time
- Pulse width control via SMC trigger input (1 ns to > 10 µs)
- Rep. rates from single shot to 35 MHz
- Single supply
- Current monitor and isolated monitor
- Applications: LIDAR, Measurements, Ignition, Rangefinding, Biochemistry, ...

Technical Data*

Output current	0.3 3 A (max. 3.5 A)**
Max. output voltage	80 V
- int. high voltage	0 80 V, 1 A, 15 W
Rise time	Typ. 800 ps, max. 1.2 ns
Trigger delay	Typ. 2.5 ns, max. 4 ns 1 ns
Min. pulse duration	
Max. pulse duration	> 10 µs**
Trigger range	Single shot to 35 MHz** (refer to diagram with
	operating limits)
Trigger input	5 V into 50 Ω via
	SMC-jack
Trigger output	Galvanically isolated
Ingger sarpar	Rogowski coil
Current monitor	2.0 A / V into 50 Ω
Supply voltage	15 24 V DC, 2.2 A
3,	
Max. power dissipation	15 W
Dimensions in mm	75 x 44 x 20
Weight	76 g
Operating temperature	-20 to +55 °C

^{*} Measured into a short instead of laser diode. Technical data is subject to change without further notice.

PicoLAS strongly recommends the use of the PLCS-21 to achieve best results.

Optional Accessories: PLCS-21

> PLB-21 LDP-V BOB LDP-V KIT

PicoLAS GmbH Burastr. 2 52146 Würselen Germany

Phone: +49 (0)2405 64594 60 +49 (0)2405 64594 61

E-mail: sales@picolas.de Web: www.picolas.de

^{**} See manual for detailed information.